

LED InstantFit Lamps

16.5T8 LED/48-4000 20/1 DC Driver

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Warnings and Safety

- Philips LED T8 InstantFit lamps will only operate properly on compatible instant-start ballasts. Please refer to the Philips LED T8 InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit www.philips.com/tled

Product data

General Information		Power Consumption	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		16.5 W
Nominal lifetime	50,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	Instant full light s
Lighting Technology	LED	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	25-27 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	160 degree(s)	T-Case Maximum (Nom)	45 °C
Luminous Flux	2,100 lm	Controls and Dimming	
Color Designation	Cool White (CW)	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	127.27 lm/W	Product Length	1,200 mm
Color Consistency	<6	Bulb Shape	Tube, double-ended
Color rendering index (CRI)	82	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and Electrical		Suitable For Accent Lighting	No
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

LED InstantFit Lamps


Approval Marks	CE marking UL certificate RoHS compliance
	KEMA Keur certificate
Energy Consumption kWh/1000 h	21 kWh

Product Data

Order product name	16.5T8 LED/48-4000 20/1 DC Driver
Full product name	16.5T8 LED/48-4000 20/1 DC Driver
Order code	929001175104


Material Nr. (12NC)	929001175104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677458126
Numerator - Packs per outer box	20
EAN/UPC - Case	50046677458121

Dimensional drawing



Product	D1	D2	A1	A2	A3
16.5T8 LED/48-4000 20/1 DC Driver	25.68 mm	28 mm	1,198.0 mm	1,205.0 mm	1,212.0 mm

Photometric data



Light Distribution Diagram - 16.5T8 LED/48-4000 20/1 DC Driver

Spectral Power Distribution Colour - 16.5T8 LED/48-4000 20/1 DC Driver

