



LED InstantFit Lamps

10.5PL-C/T LED/26V-3000 IF 4P 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Warnings and Safety

- Perform a visual inspection to ensure lamp holders (or sockets) are not damaged or loose. If the lamp holders (or sockets) are damaged, corroded, charred, blackened or loose, contact a qualified electrician for proper replacement.
- Please refer to the ballast compatibility guide located at www.philips.com/instantfit.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	GX24Q-3 [GX24q-3]	Warm-up time to 60% light		Instant full light s
Nominal lifetime	40,000 hour(s)	Power Factor (Fraction)		0.9
Switching Cycle	50,000	Voltage (Nom)		120-277 V
Lighting Technology	LED	Temperature		
EU RoHS compliant	Yes	Ambient temperature range		-4 °F to 95 °F
Light Technical		T-Case Maximum (Nom)		171 °F
Color Code	830 [CCT of 3000K]	Controls and Dimming		
Beam Angle (Nom)	120 degree(s)	Dimmable		No
Luminous Flux	1,200 lm	Mechanical and Housing		
Correlated Color Temperature (Nom)	3000 K	Product Length		100 mm
Color Consistency	<6	Approval and Application		
Color rendering index (CRI)	82	Energy Saving Product		Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting		No
Operating and Electrical		Approval Marks		CE marking UL certificate RoHS compliance KEMA Keur certificate
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Power Consumption	10.5 W			

LED InstantFit Lamps

Energy Consumption kWh/1000 h	14.5 kWh
Product Data	
Order product name	10.5PL-C/T LED/26V-3000 IF 4P 10/1
Full product name	10.5PL-C/T LED/26V-3000 IF 4P 10/1
Order code	458414
Material Nr. (12NC)	929001181204


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677458416
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677458411

Dimensional drawing




Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-3000 IF 4P 10/1	1 inch	1-3/16 inch	3-15/16 inch	4-3/8 inch	5 inch

Photometric data



Light Distribution Diagram - 10.5PL-C/T LED/26V-3000 IF 4P 10/1



Spectral Power Distribution Colour - 10.5PL-C/T LED/26V-3000 IF 4P 10/1

