

CorePro Plastic LEDbulbs

Corepro LEDbulb ND 6.5-40W E27 A60 CL

CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	72.3 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	6.5 W


Lamp Current (Nom)	55 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]
Approval and Application	
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	7 kWh

CorePro Plastic LEDbulbs

Product Data	
Order product name	Corepro LEDbulb ND 6.5-40W E27 A60 CL
Full product name	Corepro LEDbulb ND 6.5-40W E27 A60 CL
Full product code	871869651587700
Order code	51587700
Material Nr. (12NC)	929001182302


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696515877
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696515884

Dimensional drawing




Product	D	C
Corepro LEDbulb ND 6.5-40W E27 A60 CL	60 mm	110 mm

Photometric data



Light Distribution Diagram - Corepro LEDbulb ND 6.5-40W E27 A60 CL



Spectral Power Distribution Colour - Corepro LEDbulb ND 6.5-40W E27 A60 CL

