



Classic filament LEDbulbs

CLA LEDCandle ND 2.3-25W E14 WW ST35 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	2.3 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	65 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ST35


Approval and Application	
Suitable For Accent Lighting	No

Classic filament LEDbulbs

Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	CLA LEDCandle ND 2.3-25W E14 WW ST35 CL
Full product name	CLA LEDCandle ND 2.3-25W E14 WW ST35 CL
Full product code	871869652382700
Order code	929001190102


Material Nr. (12NC)	929001190102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696523827
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696523834

Dimensional drawing




Product	D	C
CLA LEDCandle ND 2.3-25W E14 WW ST35 CL	35 mm	97 mm

Photometric data



Light Distribution Diagram - CLA LEDCandle ND 2.3-25W E14 WW ST35 CL



Spectral Power Distribution Colour - CLA LEDCandle ND 2.3-25W E14 WW ST35 CL

