





CorePro LED PLC 6.5W 830 4P G24q-2

The CorePro LED PLC 4P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplamping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data

General Information			
Cap-Base	G24q-2		
Nominal lifetime	30,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
Flux measurement reference	Sphere		
CE mark	Yes		
EU RoHS compliant	Yes		
Light Technical			
Color Code	830 [CCT of 3000K]		
Beam Angle (Nom)	120 degree(s)		
Luminous Flux	650 lm		
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	92.31 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	83		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Photobiological safety according to EN 62471	RG0		
Operating and Electrical			
Line Frequency	30000-80000 Hz		


Input Frequency	30000-80000 Hz
Power Consumption	6.5 W
Lamp Current (Max)	300 mA
Lamp Current (Min)	150 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	20-50 V
LED alternative to fluorescent lamp power	18 W
Inrush current at mains	-
Max. lamp no. on MCB B type 10A - Mains	=
Max. lamp no. on MCB B type 10A – EM ballast	=
without Comp. Cap.	
Max. lamp no. on MCB B type 10A – EM ballast	=
with Comp. Cap.	
Max. lamp no. on MCB B type 16A - Mains	-
Max. lamp no. on MCB B type 16A – EM ballast	-
without Comp. Cap.	
Max. lamp no. on MCB B type 16A – EM ballast	-
with Comp. Cap.	
Ballast Compatibility	HF
·	·

Datasheet, 2024, March 19 data subject to change

Temperature	
Ambient temperature range	-20 °C to 35 °C
T-Case Maximum (Nom)	66 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Plastic
Product Length	100 mm
Bulb Shape	PL-C
Approval and Application	
Energy Efficiency Class	F
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance
	KEMA Keur certificate


Energy Consumption kWh/1000 h	7 kWh		
EPREL Registration Number	403552		
Product Data			
Order product name	CorePro LED PLC 6.5W 830 4P		
	G24q-2		
Full product name	CorePro LED PLC 6.5W 830 4F		
	G24q-2		
Full product code	871869654119700		
Order code	929001201002		
Material Nr. (12NC)	929001201002		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718696541197		
Numerator - Packs per outer box	10		
EAN/UPC - Case	8718696541203		

Dimensional drawing




Product	D1	D2	A1	A2	А3
CorePro LED PLC 6.5W 830 4P	24.3 mm	28.4 mm	105.8 mm	125 mm	140.6 mm
G24q-2					

Photometric data






General uniform lighting - CorePro LED PLC 6.5W 830 4P G24q-2




Light Distribution Diagram - CorePro LED PLC 6.5W 830 4P G24q-2


Photometric data




Spectral Power Distribution Colour - CorePro LED PLC 6.5W 830 4P G24q-2

Lifetime






Life Expectancy Diagram - CorePro LED PLC 6.5W 830 4P G24q-2




Life Expectancy Diagram - CorePro LED PLC 6.5W 830 4P G24q-2



Life Expectancy Diagram - CorePro LED PLC 6.5W 830 4P G24q-2

Lumen Maintenance Diagram - CorePro LED PLC 6.5W 830 4P G24q-2

Lifetime



Lumen Maintenance Diagram - CorePro LED PLC 6.5W 830 4P G24q-2



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.