



CorePro Plastic LEDcandles & lusters

Corepro candle ND 5.5-40W E14 840 B35 CL

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data


General Information			
Cap-Base	E14 [E14]	Power Consumption	5.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	50 mA
Switching Cycle	50,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	85 °C
Luminous Flux	520 lm		
Color Designation	Cool White (CW)	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	94.55 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	B35 [B 35mm]
Operating and Electrical		Approval and Application	
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	6 kWh
Input Frequency	50 to 60 Hz		

CorePro Plastic LEDcandles & lusters

EyeComfort	Yes
Product Data	
Order product name	Corepro candle ND 5.5-40W E14 840 B35 CL
Full product name	Corepro candle ND 5.5-40W E14 840 B35 CL
Full product code	871869654340500
Order code	54340500



Material Nr. (12NC)	929001206002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696543405
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696543412

Dimensional drawing



Product	D	C
Corepro candle ND 5.5-40W E14 840 B35 CL	35 mm	106 mm

Photometric data



General uniform lighting - Corepro candle ND 5.5-40W E14 840 B35 CL

Light Distribution Diagram - Corepro candle ND 5.5-40W E14 840 B35 CL



Spectral Power Distribution Colour - Corepro candle ND 5.5-40W E14 840 B35 CL

CorePro Plastic LEDcandles & lusters

Lifetime



Life Expectancy Diagram - Corepro candle ND 5.5-40W E14 840 B35 CL



Lumen Maintenance Diagram - Corepro candle ND 5.5-40W E14 840 B35 CL

