



# LED A15

## 5.5A15/LED/827-22/E12/CL/DIM 120V

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

### Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux	450 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	81.82 lm/W
Color Consistency	ANSI 2700K
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A15 [A 15mm]

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star


Product Data	
Order product name	5.5A15/LED/827-22/E12/CL/DIM 120V
Full product name	5.5A15/LED/827-22/E12/CL/DIM 120V
Order code	929001213304

# LED A15

Material Nr. (12NC)	929001213304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677463984
Numerator - Packs per outer box	10



EAN/UPC - Case	50046677463989
----------------	----------------

## Dimensional drawing





Product	D	C
5.5A15/LED/827-22/E12/CL/DIM 120V	50 mm	91 mm

## Photometric data



Spectral Power Distribution Colour - 5.5A15/LED/827-22/E12/CL/DIM 120V

General uniform lighting - 5.5A15/LED/827-22/E12/CL/DIM 120V



Light Distribution Diagram - 5.5A15/LED/827-22/E12/CL/DIM 120V

Spectral Power Distribution Colour - 5.5A15/LED/827-22/E12/CL/DIM 120V

## LED A15

