



# MASTER VALUE LEDspot MV

## MAS LEDspotMV VLE D 3.5-35W GU10 827 40D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	35,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	305 lm

Luminous Intensity (Nom)	550 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	87.14 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	265 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz

MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Lamp Current (Nom)	19 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------

Approval and Application


Energy Saving Product	Yes
-----------------------	-----

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh
EyeComfort	Yes

Product Data


Order product name	MAS LEDspotMV VLE D 3.5-35W GU10 827 40D
Full product name	MAS LEDspotMV VLE D 3.5-35W GU10 827 40D
Full product code	871869656298700
Order code	929001215502
Material Nr. (12NC)	929001215502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696562987
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696562994

Dimensional drawing




Product	D	C
MAS LEDspotMV VLE D 3.5-35W GU10 827 40D	50 mm	56 mm

Photometric data



Spectral Power Distribution Colour - MAS LEDspotMV VLE D 3.5-35W GU10 827 40D



Light Distribution Diagram - MAS LEDspotMV VLE D 3.5-35W GU10 827 40D

# MASTER VALUE LEDspot MV

## Photometric data

