



MASTER VALUE LEDspot MV

MASTER LEDspotMV VLE D 4.3-50W GU10 827 60D

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime	35,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	60 degree(s)

Luminous Flux	420 lm
Luminous intensity (nom.)	450 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	97.67 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	365 lm

MASTER VALUE LEDspot MV

Operating and Electrical

Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4.3 W
Lamp current (nom.)	24 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V

Temperature

T-Case maximum (nom.)	80 °C
-----------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb shape	PAR16 [PAR 2 inch/50 mm]
------------	--------------------------


Approval and Application

Energy-saving product	Yes
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	5 kWh

Product Data



Order product name	MAS LEDspotMV VLE D 4.3-50W GU10 827 60D
Full product name	MASTER LEDspotMV VLE D 4.3-50W GU10 827 60D
Full EOC	871869656312000
Order code	56312000
Material no. (12 NC)	929001216402
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696563120
Numerator – packs per outer box	10
EAN/UPC - Case	8718696563137

Dimensional drawing



Product	D	C
MAS LEDspotMV VLE D 4.3-50W GU10 827 60D	50 mm	56 mm

Photometric data




Spectral Power Distribution Colour - MAS LEDspotMV VLE D 4.3-50W GU10 827 60D

Light Distribution Diagram - MAS LEDspotMV VLE D 4.3-50W GU10 827 60D

MASTER VALUE LEDspot MV

Photometric data



General uniform lighting - MAS LEDspotMV VLE D 4.3-50W GU10 827 60D

