



Classic LEDspotMV

CorePro LEDspot 5-50W GU10 827 36D DIM

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

Product data

General Information	
Cap base	GU10 [GU10]
RoHS mark	RoHS mark
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	5-50W
Light Technical	
Colour code	827 [CCT of 2,700 K]
Beam Angle (Nom)	36 °
Luminous flux (nom.)	350 lm
Luminous flux (rated) (nom.)	350 lm
Luminous intensity (nom.)	650 cd
Colour designation	Warm white (WW)
Rated beam angle	36 °
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	70.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	350 lm


Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W
Lamp current (nom.)	30 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	1 s
Power factor (nom.)	0.70
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869656560500

Classic LEDspotMV

Order product name	CorePro LEDspot 5-50W GU10 827 36D DIM
EAN/UPC – product	8718696565605
Order code	56560500
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001218802
Net weight (piece)	0.036 kg


Dimensional drawing




GU10 230V 5W-50W 385lm 60D 3000K GU10 ND

Product	D	C
CorePro LEDspot 5-50W GU10 827 36D DIM	50 mm	53 mm


Photometric data



LEDspotMV GU10 MR16 827



LEDspotMV 5.5W-50W GU10 827 36D



LEDspotMV 5.5W-50W GU10 827 36D

Classic LEDspotMV

