



# PAR30/PAR20 LED

## 120V PAR20 SO 6W 35D 2700K DIM

Philips PAR30S LED Single Optic Lamps with AirFlux Technology provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.


### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	6-50W
Light Technical	
Color Code	827 [ CCT of 2700K]
Beam Angle (Nom)	35 °
Luminous Flux (Nom)	480 lm
Luminous Flux (Rated) (Nom)	480 lm
Luminous Intensity (Nom)	1000 cd
Color Designation	Warm White (WW)
Rated Beam Angle	35 °
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	6 W
Lamp Current (Nom)	55 mA
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes
Product Data	
Order product name	120V PAR20 SO 6W 35D 2700K DIM
EAN/UPC - Product	046677463670
Order code	929001225304
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001225304
Net Weight (Piece)	0.001 kg

# PAR30/PAR20 LED



## Dimensional drawing




PAR20 120V 6W-50W 480lm 35D 2700K E26 D

Product	D	C
120V PAR20 SO 6W 35D 2700K DIM	63.2 mm	82.6 mm

## Photometric data



Accent Lighting - Spots



LEDlamps 6-50W PAR20 E26 35D 2700K 480lm

## PAR30/PAR20 LED

