



Classic filament LED candles and lustres

Classic LEDCandle D 2.5-25W B35 E14 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

Product data


General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	300 lm
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz

Power Consumption	3 W
Lamp current (nom.)	19 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	B35 [B 35 mm]
Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No
Energy consumption kWh/1,000 hours	3 kWh


Classic filament LED candles and lustres

Product Data	
Order product name	CLA LEDCandle D 3-25W B35 E14 827 CL
Full product name	Classic LEDCandle D 2.5-25W B35 E14 827 CL
Full EOC	871869657553600
Order code	57553600
Material no. (12 NC)	929001227002
Local order code	LF3WE14CNDLD

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDCandle D 3-25W B35 E14 827 CL

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696575536
Numerator – packs per outer box	10
EAN/UPC - Case	8718696575543

Product	D	C
CLA LEDCandle D 3-25W B35 E14 827 CL	35 mm	118 mm



General uniform lighting - CLA LEDCandle D 3-25W B35 E14 827 CL



Light Distribution Diagram - CLA LEDCandle D 3-25W B35 E14 827 CL

Classic filament LED candles and lustres

