

Classic filament LED candles and lusters

CLA LEDCandle D 4.5-40W BA35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	104.44 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	4.5 W
Lamp Current (Nom)	29 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	BA35
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	5 kWh


Datasheet, 2023, October 26 data subject to change

Classic filament LED candles and lusters

Product Data	
Order product name	CLA LEDCandle D 4.5-40W BA35 E14 827 CL
Full product name	CLA LEDCandle D 4.5-40W BA35 E14 827 CL
Full product code	871869657557400
Order code	929001227302
Material Nr. (12NC)	929001227302


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696575574
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696575581

Dimensional drawing




Product	D	С
CLA LEDCandle D 4.5-40W BA35 E14 827 CL	35 mm	144 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDCandle D 4.5-40W BA35 E14 827 CL



General uniform lighting - CLA LEDCandle D 4.5-40W BA35 E14 827 CL



Light Distribution Diagram - CLA LEDCandle D 4.5-40W BA35 E14 827 CL

Classic filament LED candles and lusters



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.