



Classic filament LED candles and lustres

Classic LEDCandle D 4.5-40W B35 B22 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.


Product data

General Information			
Cap base	B22 [B22]	Power Consumption	4.5 W
Nominal lifetime	15,000 h	Lamp current (nom.)	29 mA
Switching Cycle	20,000	Wattage equivalent	40 W
Lighting Technology	LED	Starting time (nom.)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (nom.)	220-240 V
Light Technical		Controls and Dimming	
Colour Code	827 [CCT of 2700K]	Dimmable	Yes
Luminous Flux	470 lm		
Colour designation	Warm White (WW)	Mechanical and Housing	
Correlated Colour Temperature	2700 K	Lamp Finish	Clear
Luminous efficacy (rated) (nom.)	104.44 lm/W	Bulb shape	B35 [B 35 mm]
Colour consistency	<6		
Colour rendering index (CRI)	80	Approval and Application	
LLMF at end of nominal lifetime (nom.)	70 %	Energy-saving product	Yes
		Suitable for accent lighting	No
Operating and Electrical		Energy consumption kWh/1,000 hours	5 kWh
Line Frequency	50 to 60 Hz		
Input frequency	50 to 60 Hz		


Classic filament LED candles and lustres

Product Data	
Order product name	CLA LEDCandle D 4.5-40W B35 B22 827 CL
Full product name	Classic LEDCandle D 4.5-40W B35 B22 827 CL
Full EOC	871869657563500
Order code	57563500
Material no. (12 NC)	929001227502

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDCandle D 4.5-40W B35 B22 827 CL

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696575635
Numerator – packs per outer box	10
EAN/UPC - Case	8718696575642

Product	D	C
CLA LEDCandle D 4.5-40W B35 B22 827 CL	35 mm	104 mm



General uniform lighting - CLA LEDCandle D 4.5-40W B35 B22 827 CL



Light Distribution Diagram - CLA LEDCandle D 4.5-40W B35 B22 827 CL

Classic filament LED candles and lustres

