

Classic filament LEDbulbs

CLA LEDBulb D 4.5-40W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.


Product data

General Information			
Cap base	E27 [E27]	Power Consumption	4.5 W
Nominal lifetime	15,000 h	Lamp current (nom.)	29 mA
Switching Cycle	20,000	Wattage equivalent	40 W
Lighting Technology	LED	Starting time (nom.)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (nom.)	220-240 V
Light Technical			
Colour Code	827 [CCT of 2700K]	Controls and Dimming	
Luminous Flux	470 lm	Dimmable	Yes
Colour designation	Warm White (WW)		
Correlated Colour Temperature	2700 K	Mechanical and Housing	
Luminous efficacy (rated) (nom.)	104.44 lm/W	Lamp Finish	Clear
Colour consistency	<6	Bulb shape	A60 [A 60 mm]
Colour rendering index (CRI)	80		
LLMF at end of nominal lifetime (nom.)	70 %	Approval and Application	
		Energy-saving product	Yes
Operating and Electrical		Suitable for accent lighting	No
Line Frequency	50 to 60 Hz	Energy consumption kWh/1,000 hours	5 kWh
Input frequency	50 to 60 Hz		


Classic filament LEDbulbs

Product Data	
Order product name	CLA LEDBulb D 4.5-40W A60 E27 827 CL
Full product name	CLA LEDBulb D 4.5-40W A60 E27 827 CL
Full EOC	871869657545100
Order code	57545100
Material no. (12 NC)	929001227902

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDBulb D 4.5-40W A60 E27 827 CL

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696575451
Numerator – packs per outer box	10
EAN/UPC - Case	8718696575468

Product	D	C
CLA LEDBulb D 4.5-40W A60 E27 827 CL	60 mm	112 mm



General uniform lighting - CLA LEDBulb D 4.5-40W A60 E27 827 CL



Light Distribution Diagram - CLA LEDBulb D 4.5-40W A60 E27 827 CL

Classic filament LEDbulbs

