

# Classic filament LEDbulbs

## CLA LEDBulb D 4.5-40W A60 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.


### Product data

General Information			
Cap-Base	E27 [E27]	Power Consumption	4.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	29 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.7
Color Code	827 [CCT of 2700K]	Voltage (Nom)	220-240 V
Luminous Flux	470 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	104.44 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Shape	A60 [A 60mm]
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	Yes
Operating and Electrical		Suitable For Accent Lighting	No
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	5 kWh
Input Frequency	50 to 60 Hz		


Classic filament LEDbulbs

Product Data	
Order product name	CLA LEDBulb D 4.5-40W A60 E27 827 CL
Full product name	CLA LEDBulb D 4.5-40W A60 E27 827 CL
Full product code	871869657545100
Order code	929001227902
Material Nr. (12NC)	929001227902

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDBulb D 4.5-40W A60 E27 827 CL

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696575451
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696575468

Product	D	C
CLA LEDBulb D 4.5-40W A60 E27 827 CL	60 mm	112 mm



General uniform lighting - CLA LEDBulb D 4.5-40W A60 E27 827 CL



Light Distribution Diagram - CLA LEDBulb D 4.5-40W A60 E27 827 CL

## Classic filament LEDbulbs

