



Classic filament LEDbulbs

CLA LEDBulb D 4.5-40W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.


Product data

General Information		Power Consumption	
Cap base	B22 [B22]	4.5 W	
Nominal lifetime	15,000 h	Lamp current (nom.)	
Switching Cycle	20,000	29 mA	
Lighting Technology	LED	Starting time (nom.)	
EU RoHS compliant	Yes	0.5 s	
Light Technical		Warm-up time to 60% light	
Colour Code	827 [CCT of 2700K]	0.5 s	
Luminous Flux	470 lm	Power Factor (Fraction)	
Colour designation	Warm White (WW)	0.7	
Correlated Colour Temperature	2700 K	Voltage (nom.)	
Luminous efficacy (rated) (nom.)	104.44 lm/W	220-240 V	
Colour consistency	<6	Controls and Dimming	
Colour rendering index (CRI)	80	Dimmable	
LLMF at end of nominal lifetime (nom.)	70 %	Yes	
Operating and Electrical		Mechanical and Housing	
Line Frequency	50 to 60 Hz	Lamp Finish	
Input frequency	50 to 60 Hz	Clear	
		Bulb shape	
		A60 [A 60 mm]	
		Approval and Application	
		Energy-saving product	
		Yes	
		Suitable for accent lighting	
		No	
		Energy consumption kWh/1,000 hours	
		5 kWh	


Classic filament LEDbulbs

Product Data	
Order product name	CLA LEDBulb D 4.5-40W A60 B22 827 CL
Full product name	CLA LEDBulb D 4.5-40W A60 B22 827 CL
Full EOC	871869657549900
Order code	57549900
Material no. (12 NC)	929001228202

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDBulb D 4.5-40W A60 B22 827 CL

SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696575499
Numerator – packs per outer box	10
EAN/UPC - Case	8718696575505

Product	D	C
CLA LEDBulb D 4.5-40W A60 B22 827 CL	60 mm	110.5 mm



General uniform lighting - CLA LEDBulb D 4.5-40W A60 B22 827 CL



Light Distribution Diagram - CLA LEDBulb D 4.5-40W A60 B22 827 CL

Classic filament LEDbulbs

