



# Classic filament LEDbulbs

## LEDClassic 7-70W ST64 E27 WW CL D APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ST64

# Classic filament LEDbulbs

## Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	7 kWh

## Product Data


Order product name	LEDClassic 7-70W ST64 E27 WW CL D APR
Full product name	LEDClassic 7-70W ST64 E27 WW CL D APR
Full product code	871869657487400

Order code	929001228608
Material Nr. (12NC)	929001228608
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574874
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574881


## Dimensional drawing

Product	D	C
LEDClassic 7-70W ST64 E27 WW CL D APR	64 mm	148 mm


## Photometric data



Spectral Power Distribution Colour - LEDClassic 7-70W ST64 E27 WW CL D APR



General uniform lighting - LEDClassic 7-70W ST64 E27 WW CL D APR



Light Distribution Diagram - LEDClassic 7-70W ST64 E27 WW CL D APR

## Classic filament LEDbulbs

