



# CorePro LEDspot Reflectors

## CorePro LEDspotMV D 5-60W 827 R50 36D

CorePro LEDspots Reflectors are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with an E27 or E14 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots Reflectors deliver significant energy savings and minimise maintenance costs.

### Product data

General Information	
Cap base	E14 [E14]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	320 lm
Luminous intensity (nom.)	735 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	64.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	320 lm


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	5 W
Lamp current (nom.)	27 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.5
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	82 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	R50 [R 50 mm]

CorePro LEDspot Reflectors

Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	5 kWh

Product Data	
Order product name	CorePro LEDspotMV D 5-60W 827 R50 36D
Full product name	CorePro LEDspotMV D 5-60W 827 R50 36D
Full EOC	871869657853700



Dimensional drawing



Order code	57853700
Material no. (12 NC)	929001236002
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696578537
Numerator – packs per outer box	6
EAN/UPC – Case	8718696578544


Product	D	C
CorePro LEDspotMV D 5-60W 827 R50 36D	51 mm	81 mm

Photometric data



Spectral Power Distribution Colour - CorePro LEDspotMV D 5-60W 827 R50 36D

General uniform lighting - CorePro LEDspotMV D 5-60W 827 R50 36D



Light Distribution Diagram - CorePro LEDspotMV D 5-60W 827 R50 36D

## CorePro LEDspot Reflectors

