

Classic filament LEDbulbs

LEDClassic 4-50W A60 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)		33 mA
Cap-Base	E27 [E27]	Wattage Equivalent		50 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	20,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)		0.4
Lighting Technology	LED	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)		70 °C
Luminous Flux	470 lm	Controls and Dimming		
Color Designation	Warm White (WW)	Dimmable		No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	118.00 lm/W	Bulb Finish		Clear
Color Consistency	<6	Bulb Shape		A60 [A 60mm]
Color rendering index (CRI)	80	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product		Yes
Operating and Electrical		Suitable For Accent Lighting		No
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h		4 kWh
Input Frequency	50 to 60 Hz			
Power Consumption	4 W			

Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 4-50W A60 E27 WW CL ND APR
Full product name	LEDClassic 4-50W A60 E27 WW CL ND APR
Full product code	871869657419500
Order code	57419500
Material Nr. (12NC)	929001237108


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574195
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696574201

Dimensional drawing




Product	D	C
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 4-50W A60 E27 WW CL ND APR



General uniform lighting - LEDClassic 4-50W A60 E27 WW CL ND APR



Light Distribution Diagram - LEDClassic 4-50W A60 E27 WW CL ND APR

Classic filament LEDbulbs

