

# Classic filament LEDbulbs

## CLA LEDBulb ND 6-60W ST64 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.


### Product data

<b>General Information</b>			
Cap-Base	E27 [E27]	Power Consumption	6 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	52 mA
Switching Cycle	20,000	Wattage Equivalent	60 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
<b>Light Technical</b>			
Color Code	827 [CCT of 2700K]	<b>Controls and Dimming</b>	
Luminous Flux	806 lm	Dimmable	No
Color Designation	Warm White (WW)	<b>Mechanical and Housing</b>	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Clear
Luminous Efficacy (rated) (Nom)	134.00 lm/W	Bulb Shape	ST64
Color Consistency	<6	<b>Approval and Application</b>	
Color rendering index (CRI)	80	Energy Saving Product	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting	No
<b>Operating and Electrical</b>		Energy Consumption kWh/1000 h	6 kWh
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Product Data	
Order product name	CLA LEDBulb ND 6-60W ST64 E27 827 CL
Full product name	CLA LEDBulb ND 6-60W ST64 E27 827 CL
Full product code	871869657405800
Order code	929001237402
Material Nr. (12NC)	929001237402


Dimensional drawing




Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574058
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574065

Product	D	C
CLA LEDBulb ND 6-60W ST64 E27 827 CL	64 mm	140 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb ND 6-60W ST64 E27 827 CL




General uniform lighting - CLA LEDBulb ND 6-60W ST64 E27 827 CL




Light Distribution Diagram - CLA LEDBulb ND 6-60W ST64 E27 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 6-60W ST64 E27 827 CL



Lumen Maintenance Diagram - CLA LEDBulb ND 6-60W ST64 E27 827 CL

