

Classic filament LEDbulbs

LEDClassic6-70W ST64 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


| | | | |
|---------------------------------------|--------------------|---------------------------------------|--|
| General Information | | Wattage Equivalent | |
| Cap-Base | E27 [E27] | 70 W | |
| Nominal lifetime | 15,000 hour(s) | Starting Time (Nom) | |
| Switching Cycle | 20,000 | 0.5 s | |
| Lighting Technology | LED | Warm-up time to 60% light | |
| EU RoHS compliant | Yes | 0.5 s | |
| Light Technical | | Power Factor (Fraction) | |
| Color Code | 827 [CCT of 2700K] | 0.5 | |
| Luminous Flux | 806 lm | Voltage (Nom) | |
| Color Designation | Warm White (WW) | 220-240 V | |
| Correlated Color Temperature (Nom) | 2700 K | Controls and Dimming | |
| Luminous Efficacy (rated) (Nom) | 134.00 lm/W | Dimmable | |
| Color Consistency | <6 | No | |
| Color rendering index (CRI) | 80 | Mechanical and Housing | |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | Bulb Finish | |
| Operating and Electrical | | Clear | |
| Line Frequency | 50 to 60 Hz | Bulb Shape | |
| Input Frequency | 50 to 60 Hz | ST64 | |
| Power Consumption | 6 W | Approval and Application | |
| Lamp Current (Nom) | 52 mA | Energy Saving Product | |
| | | Yes | |
| | | Product Data | |
| | | Order product name | |
| | | LEDClassic6-70W ST64 E27 WW CL ND APR | |
| | | Full product name | |
| | | LEDClassic6-70W ST64 E27 WW CL ND APR | |
| | | Full product code | |
| | | 871869657425600 | |

Classic filament LEDbulbs

| | |
|-------------------------------|---------------|
| Order code | 57425600 |
| Material Nr. (12NC) | 929001237408 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696574256 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 6 |
| EAN/UPC - Case | 8718696574263 |

Dimensional drawing




| Product | D | C |
|---------------------------------------|-------|--------|
| LEDClassic6-70W ST64 E27 WW CL ND APR | 64 mm | 140 mm |


Photometric data



Spectral Power Distribution Colour - LEDClassic6-70W ST64 E27 WW CL ND APR



General uniform lighting - LEDClassic6-70W ST64 E27 WW CL ND APR




Light Distribution Diagram - LEDClassic6-70W ST64 E27 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic6-70W ST64 E27 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic6-70W ST64 E27 WW CL ND APR

