



Classic filament LED candles and lusters

Classic LEDCandle ND 2-25W ST35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data


General Information		Power Consumption	
Cap-Base	E14 [E14]	Lamp Current (Nom)	20 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	25 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	97 °F
Luminous Flux	250 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	80	Bulb Shape	ST35
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Energy Saving Product	Yes
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LED candles and lusters

Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EyeComfort	Yes
Product Data	
Order product name	CLA LEDCandle ND 2-25W ST35 E14 827 CL
Full product name	Classic LEDCandle ND 2-25W ST35 E14 827 CL
Full product code	871869657411900



Order code	324467
Material Nr. (12NC)	929001238502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574119
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574126

Dimensional drawing




Product	D	C
CLA LEDCandle ND 2-25W ST35 E14 827 CL	1-3/8 inch	3-13/16 inch

Photometric data



Spectral Power Distribution Colour - CLA LEDCandle ND 2-25W ST35 E14 827 CL

General uniform lighting - CLA LEDCandle ND 2-25W ST35 E14 827 CL



Light Distribution Diagram - CLA LEDCandle ND 2-25W ST35 E14 827 CL

Classic filament LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 2-25W ST35 E14 827 CL

Lumen Maintenance Diagram - CLA LEDCandle ND 2-25W ST35 E14 827 CL

