



Classic filament LED candles and lusters

CLA LEDLuster ND 2-25W P45 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data


General Information		Power Consumption	
Cap-Base	E14 [E14]	2 W	
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	
Switching Cycle	20,000	20 mA	
Lighting Technology	LED	Wattage Equivalent	
EU RoHS compliant	Yes	25 W	
Light Technical		Starting Time (Nom)	
Color Code	827 [CCT of 2700K]	0.5 s	
Luminous Flux	250 lm	Warm-up time to 60% light	
Color Designation	Warm White (WW)	0.5 s	
Correlated Color Temperature (Nom)	2700 K	Power Factor (Fraction)	
Luminous Efficacy (rated) (Nom)	125.00 lm/W	0.4	
Color Consistency	<6	Voltage (Nom)	
Color rendering index (CRI)	80	220-240 V	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Temperature	
Operating and Electrical		T-Case Maximum (Nom)	
Line Frequency	50 to 60 Hz	36 °C	
Input Frequency	50 to 60 Hz	Controls and Dimming	
		Dimmable	
		No	
		Mechanical and Housing	
		Bulb Finish	
		Clear	
		Bulb Shape	
		P45 [P 45mm]	
		Approval and Application	
		Energy Consumption kWh/1000 h	
		2 kWh	

Classic filament LED candles and lusters

EyeComfort	Yes
Product Data	
Order product name	CLA LEDLuster ND 2-25W P45 E14 827 CL
Full product name	CLA LEDLuster ND 2-25W P45 E14 827 CL
Full product code	871869657413300
Order code	929001238602


Material Nr. (12NC)	929001238602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574133
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574140

Dimensional drawing




Product	D	C
CLA LEDLuster ND 2-25W P45 E14 827 CL	45 mm	80 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDLuster ND 2-25W P45 E14 827 CL



Light Distribution Diagram - CLA LEDLuster ND 2-25W P45 E14 827 CL



General uniform lighting - CLA LEDLuster ND 2-25W P45 E14 827 CL

Classic filament LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDLuster ND 2-25W P45 E14 827 CL



Lumen Maintenance Diagram - CLA LEDLuster ND 2-25W P45 E14 827 CL

