



Classic filament LEDbulbs

LEDClassic 2-25W P45 E14 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data


General Information		Lamp Current (Nom)		20 mA
Cap-Base	E14 [E14]	Wattage Equivalent		25 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)		0.5 s
Switching Cycle	20,000	Warm-up time to 60% light		0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Power Factor (Fraction)		0.4
Lighting Technology	LED	Voltage (Nom)		220-240 V
EU RoHS compliant	Yes			
Light Technical		Temperature		
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)		70 °C
Luminous Flux	250 lm	Controls and Dimming		
Color Designation	Warm White (WW)	Dimmable		No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	125.00 lm/W	Bulb Finish		Clear
Color Consistency	<6	Bulb Shape		P45 [P 45mm]
Color rendering index (CRI)	80	Approval and Application		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h		2 kWh
Operating and Electrical		Product Data		
Line Frequency	50 to 60 Hz	Order product name		LEDClassic 2-25W P45 E14 WW CL ND APR
Input Frequency	50 to 60 Hz			
Power Consumption	2 W			

Classic filament LEDbulbs

Full product name	LEDClassic 2-25W P45 E14 WW CL ND APR
Full product code	871869657431700
Order code	57431700
Material Nr. (12NC)	929001238608
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718696574317
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574324

Dimensional drawing




Product	D	C
LEDClassic 2-25W P45 E14 WW CL ND APR	45 mm	80 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 2-25W P45 E14 WW CL ND APR



Light Distribution Diagram - LEDClassic 2-25W P45 E14 WW CL ND APR



General uniform lighting - LEDClassic 2-25W P45 E14 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 2-25W P45 E14 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 2-25W P45 E14 WW CL ND APR

