



Classic filament LEDbulbs

CLA LEDGlobe ND 6-60W G93 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	134.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	6 W
Lamp Current (Nom)	52 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G93 [G 93mm]

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	6 kWh

Classic filament LEDbulbs

Product Data	
Order product name	CLA LEDGlobe ND 6-60W G93 E27 827 CL
Full product name	CLA LEDGlobe ND 6-60W G93 E27 827 CL
Full product code	871869657417100
Order code	929001238802
Material Nr. (12NC)	929001238802


Dimensional drawing




Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574171
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574188

Product	D	C
CLA LEDGlobe ND 6-60W G93 E27 827 CL	95 mm	140 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDGlobe ND 6-60W G93 E27 827 CL



General uniform lighting - CLA LEDGlobe ND 6-60W G93 E27 827 CL



Light Distribution Diagram - CLA LEDGlobe ND 6-60W G93 E27 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDGlobe ND 6-60W G93 E27 827 CL

Lumen Maintenance Diagram - CLA LEDGlobe ND 6-60W G93 E27 827 CL

