



Classic frosted LED Lamps

LED classic 40W A60 E27 WW FR ND 2BC/10

Featuring a classic heritage design, LED frosted Classic bulbs deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of the LED frosted Classic lamps are a perfect fit for your existing fixtures.

Product data

General Information			
Cap-Base	E27 [E27]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	5 W
Switching Cycle	30,000	Lamp Current (Nom)	35 mA
Rated Lifetime (Hours)	15,000 hour(s)	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.55
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	98 °C
Beam Angle (Nom)	300 degree(s)	Controls and Dimming	
Luminous Flux	470 lm	Dimmable	No
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	94 lm/W	Bulb Shape	A60 [A 60mm]
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	Energy Saving Product	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic frosted LED Lamps


Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	5 kWh
EyeComfort	Yes

Product Data

Order product name	LED classic 40W A60 E27 WW FR ND 2BC/10
Full product name	LED classic 40W A60 E27 WW FR ND 2BC/10
Full product code	871869642232800

Order code	929001242901
Material Nr. (12NC)	929001242901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696422328
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696422335

Dimensional drawing




Product	D	C
LED classic 40W A60 E27 WW FR ND 2BC/10	60 mm	110 mm

Photometric data

Spectral Power Distribution Colour - LED classic 40W A60 E27 WW FR ND 2BC/10


Light Distribution Diagram - LED classic 40W A60 E27 WW FR ND 2BC/10




General uniform lighting - LED classic 40W A60 E27 WW FR ND 2BC/10

Classic frosted LED Lamps

Lifetime



Life Expectancy Diagram - LED classic 40W A60 E27 WW FR ND 2BC/10



Lumen Maintenance Diagram - LED classic 40W A60 E27 WW FR ND 2BC/10

