



Classic frosted LED Lamps

LED classic 60W A60 E27 WW FR ND SRT4

Featuring a classic heritage design, LED frosted Classic bulbs deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of the LED frosted Classic lamps are a perfect fit for your existing fixtures.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	30,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Power Consumption	7 W
Lamp Current (Nom)	50 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.55
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A60 [A 60mm]


Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No

Classic frosted LED Lamps

Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	LED classic 60W A60 E27 WW FR ND SRT4
Full product name	LED classic 60W A60 E27 WW FR ND SRT4
Full product code	871869657663200
Order code	929001243001

Material Nr. (12NC)	929001243001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696576632
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696576649

Dimensional drawing




Product	D	C
LED classic 60W A60 E27 WW FR ND SRT4	60 mm	110 mm


Photometric data



Spectral Power Distribution Colour - LED classic 60W A60 E27 WW FR ND SRT4



Light Distribution Diagram - LED classic 60W A60 E27 WW FR ND SRT4



General uniform lighting - LED classic 60W A60 E27 WW FR ND SRT4

Classic frosted LED Lamps

Lifetime



Life Expectancy Diagram - LED classic 60W A60 E27 WW FR ND SRT4



Lumen Maintenance Diagram - LED classic 60W A60 E27 WW FR ND SRT4

