



# Classic frosted LED Lamps

## LED classic 40W A60 E27 WW FR D SRT4

Featuring a classic heritage design, LED frosted Classic bulbs deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of the LED frosted Classic lamps are a perfect fit for your existing fixtures.

### Product data


|                                       |                    |                                 |              |
|---------------------------------------|--------------------|---------------------------------|--------------|
| <b>General Information</b>            |                    | <b>Power Consumption</b>        |              |
| Cap-Base                              | E27 [E27]          |                                 | 6 W          |
| Nominal lifetime                      | 15,000 hour(s)     | Lamp Current (Nom)              | 30 mA        |
| Switching Cycle                       | 30,000             | Starting Time (Nom)             | 0.5 s        |
| Lighting Technology                   | LED                | Warm-up time to 60% light       | 0.5 s        |
| EU RoHS compliant                     | Yes                | Power Factor (Fraction)         | 0.55         |
| <b>Light Technical</b>                |                    | Voltage (Nom)                   | 220-240 V    |
| Color Code                            | 827 [CCT of 2700K] | <b>Temperature</b>              |              |
| Beam Angle (Nom)                      | 300 degree(s)      | T-Case Maximum (Nom)            | 98 °C        |
| Luminous Flux                         | 470 lm             | <b>Controls and Dimming</b>     |              |
| Color Designation                     | Warm White (WW)    | Dimmable                        | Yes          |
| Correlated Color Temperature (Nom)    | 2700 K             | <b>Mechanical and Housing</b>   |              |
| Luminous Efficacy (rated) (Nom)       | 78 lm/W            | Bulb Finish                     | Frosted      |
| Color Consistency                     | <6                 | Bulb Shape                      | A60 [A 60mm] |
| Color rendering index (CRI)           | 80                 | <b>Approval and Application</b> |              |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %               | Energy Saving Product           | Yes          |
| <b>Operating and Electrical</b>       |                    | Suitable For Accent Lighting    | No           |
| Line Frequency                        | 50 to 60 Hz        |                                 |              |
| Input Frequency                       | 50 to 60 Hz        |                                 |              |

Classic frosted LED Lamps

|                               |                                      |
|-------------------------------|--------------------------------------|
| Energy Consumption kWh/1000 h | 6 kWh                                |
| Product Data                  |                                      |
| Order product name            | LED classic 40W A60 E27 WW FR D SRT4 |
| Full product name             | LED classic 40W A60 E27 WW FR D SRT4 |
| Full product code             | 871869657655700                      |
| Order code                    | 929001243108                         |

|                                 |               |
|---------------------------------|---------------|
| Material Nr. (12NC)             | 929001243108  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8718696576557 |
| Numerator - Packs per outer box | 4             |
| EAN/UPC - Case                  | 8718696576564 |

Dimensional drawing




| Product                              | D     | C      |
|--------------------------------------|-------|--------|
| LED classic 40W A60 E27 WW FR D SRT4 | 60 mm | 110 mm |

Photometric data



Spectral Power Distribution Colour - LED classic 40W A60 E27 WW FR D SRT4

Light Distribution Diagram - LED classic 40W A60 E27 WW FR D SRT4



General uniform lighting - LED classic 40W A60 E27 WW FR D SRT4

## Classic frosted LED Lamps

