



Classic frosted LED Lamps

LED classic 60W A60 E27 WW FR D SRT4

Featuring a classic heritage design, LED frosted Classic bulbs deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of the LED frosted Classic lamps are a perfect fit for your existing fixtures.

Product data

| | |
|---------------------|----------------|
| General Information | |
| Cap-Base | E27 [E27] |
| Nominal lifetime | 15,000 hour(s) |
| Switching Cycle | 30,000 |
| Lighting Technology | LED |
| EU RoHS compliant | Yes |

| | |
|---------------------------------------|--------------------|
| Light Technical | |
| Color Code | 827 [CCT of 2700K] |
| Beam Angle (Nom) | 300 degree(s) |
| Luminous Flux | 806 lm |
| Color Designation | Warm White (WW) |
| Correlated Color Temperature (Nom) | 2700 K |
| Luminous Efficacy (rated) (Nom) | 101 lm/W |
| Color Consistency | <6 |
| Color rendering index (CRI) | 80 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |

| | |
|--------------------------|-------------|
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |

| | |
|---------------------------|-----------|
| Power Consumption | 8 W |
| Lamp Current (Nom) | 40 mA |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.55 |
| Voltage (Nom) | 220-240 V |

| | |
|----------------------|-------|
| Temperature | |
| T-Case Maximum (Nom) | 90 °C |

| | |
|----------------------|-----|
| Controls and Dimming | |
| Dimmable | Yes |

| | |
|------------------------|--------------|
| Mechanical and Housing | |
| Bulb Finish | Frosted |
| Bulb Shape | A60 [A 60mm] |


| | |
|------------------------------|-----|
| Approval and Application | |
| Energy Saving Product | Yes |
| Suitable For Accent Lighting | No |

Classic frosted LED Lamps

| | |
|-------------------------------|--------------------------------------|
| Energy Consumption kWh/1000 h | 8 kWh |
| Product Data | |
| Order product name | LED classic 60W A60 E27 WW FR D SRT4 |
| Full product name | LED classic 60W A60 E27 WW FR D SRT4 |
| Full product code | 871869657661800 |
| Order code | 929001243201 |

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 929001243201 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696576618 |
| Numerator - Packs per outer box | 4 |
| EAN/UPC - Case | 8718696576625 |

Dimensional drawing




| Product | D | C |
|--------------------------------------|-------|--------|
| LED classic 60W A60 E27 WW FR D SRT4 | 60 mm | 110 mm |


Photometric data



Spectral Power Distribution Colour - LED classic 60W A60 E27 WW FR D SRT4



Light Distribution Diagram - LED classic 60W A60 E27 WW FR D SRT4



General uniform lighting - LED classic 60W A60 E27 WW FR D SRT4

Classic frosted LED Lamps

