



# Standard LED candles & lusters

## LEDBulb 3.5-40W E27 6500K 100-240VG16.5

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Line Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	3.5 W
Lighting Technology	LED	Wattage Equivalent	40 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	865 [CCT of 6500K]	Power Factor (Fraction)	0.4
Beam Angle (Nom)	150 degree(s)	Voltage (Nom)	100-240 V
Luminous Flux	350 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	Bulb Finish	Frosted
Color Consistency	<7	Bulb Shape	G16.5 [G16.5]
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

Standard LED candles & lusters

Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	LEDBulb 3.5-40W E27 6500K 100-240VG16.5
Full product name	LEDBulb 3.5-40W E27 6500K 100-240VG16.5
Full product code	871869658005900
Order code	929001243471

Material Nr. (12NC)	929001243471
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696580059
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696580066

Dimensional drawing



Product	D	C
LEDBulb 3.5-40W E27 6500K 100-240VG16.5	45 mm	88 mm

