



# Standard LED candles & lusters

## LEDBulb 3.5-40W E27 6500K 100-240VG45\_BR

Standard LED candles are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving candles. They deliver huge energy savings and minimize maintenance costs. The Standard LED candle is the perfect candle for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	350 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	100.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	3.5 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100–240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	G45
Product Data	
Order product name	LEDBulb 3.5-40W E27 6500K 100-240VG45_BR
Full product name	LEDBulb 3.5-40W E27 6500K 100-240VG45_BR

Standard LED candles & lusters

Full product code	871869657645801
Order code	929001243491
Material Nr. (12NC)	929001243491
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696576458

Numerator - Packs per outer box	6
EAN/UPC - Case	8718696788639

Dimensional drawing



Product	D	C
LEDBulb 3.5-40W E27 6500K 100-240VG45_BR	45 mm	88 mm

