



# MASTER LEDspot PAR

## MASLEDspot D 8.5-75W 827WW PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.


### Product data

General Information		Operating and Electrical	
Cap base	E27 [ E27]	Colour consistency	<6
Nominal lifetime (nom.)	40000 h	Color rendering index (nom.)	80
Switching cycle	50000X	LLMF at end of nominal lifetime (nom.)	70 %
Technical type	8-75W	Luminous Flux in 90° Cone (Rated)	720 lm
Light Technical		Controls and Dimming	
Colour code	827 [ CCT of 2,700 K]	Dimmable	Yes
Beam Angle (Nom)	25 °		
Light distribution	25D [ Medium beam]		
Luminous flux (nom.)	760 lm		
Luminous flux (rated) (nom.)	760 lm		
Luminous intensity (nom.)	2600 cd		
Colour designation	Warm white (WW)		
Rated beam angle	25 °		
Correlated colour temperature (nom.)	2700 K		
Luminous efficacy (rated) (nom.)	85 lm/W		
		Input frequency	50 to 60 Hz
		Power (Rated) (Nom)	8.5 W
		Lamp current (nom.)	38 mA
		Starting time (nom.)	0.5 s
		Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.9
		Voltage (Nom)	230 V

# MASTER LEDspot PAR



Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	9 kWh
Product Data	
Full product code	871869657805600
Order product name	MASLEDspot D 8.5-75W 827WW PAR30S 25D

## Dimensional drawing




PAR30S 230V 8W-75W 635lm 25D 2700K E27 D

## Photometric data



EAN/UPC – product	8718696578056
Order code	57805600
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001244102
Net weight (piece)	0.202 kg

Product	D	C
MASLEDspot D 8.5-75W 827WW PAR30S 25D	92 mm	93 mm



PAR30S 9.5W-90W /827 25D E27 D

## MASTER LEDspot PAR

