



MASTER LEDspot PAR

MASLEDspot D 8.5-75W 840CW PAR30S 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

Product data


General Information			
Cap base	E27 [E27]	Colour consistency	<6
Nominal lifetime (nom.)	40000 h	Color rendering index (nom.)	80
Switching cycle	50000X	LLMF at end of nominal lifetime (nom.)	70 %
Technical type	8-75W	Luminous Flux in 90° Cone (Rated)	800 lm
Light Technical		Operating and Electrical	
Colour code	840 [CCT of 4,000 K]	Input frequency	50 to 60 Hz
Beam Angle (Nom)	25 °	Power (Rated) (Nom)	8.5 W
Light distribution	25D [Medium beam]	Lamp current (nom.)	38 mA
Luminous flux (nom.)	840 lm	Starting time (nom.)	0.5 s
Luminous flux (rated) (nom.)	840 lm	Warm-up time to 60% light (nom.)	0.5 s
Luminous intensity (nom.)	2800 cd	Power factor (nom.)	0.9
Colour designation	Cool White (CW)	Voltage (Nom)	230 V
Rated beam angle	25 °	Controls and Dimming	
Correlated colour temperature (nom.)	4000 K	Dimmable	yes
Luminous efficacy (rated) (nom.)	94 lm/W		

MASTER LEDspot PAR

Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	9 kWh
Product Data	
Full product code	871869657807000
Order product name	MASLEDspot D 8.5-75W 840CW PAR30S 25D

EAN/UPC – product	8718696578070
Order code	57807000
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001244202
Net weight (piece)	0.202 kg



Dimensional drawing




PAR30S 230V 8W-75W 675lm 25D 4000K E27 D

Product	D	C
MASLEDspot D 8.5-75W 840CW PAR30S 25D	92 mm	93 mm

Photometric data



PAR30S 9.5W-90W /840 25D E27 D



MASTER LEDspot PAR

