

CorePro LEDtube InstantFit HF

CorePro LEDtube HF 600mm 9W865 T8 G

CorePro LEDtube InstantFit HF is an affordable LED solution, suitable for replacing T8 fluorescent lamps. It provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.


Product data

General Information			
Cap base	G13 [Medium Bi-Pin Fluorescent]	Input frequency	20000-80000 Hz
Nominal lifetime	30,000 h	Power Consumption	9 W
Switching Cycle	50,000	Lamp current (max.)	400 mA
Lighting Technology	LED	Lamp current (min.)	200 mA
EU RoHS compliant	Yes	Starting time (nom.)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (nom.)	30-80 V
Light Technical		Temperature	
Colour Code	865 [CCT of 6500K]	Ambient temperature range	-20°C to 45°C
Beam angle (nom.)	240 degree(s)	T-Case maximum (nom.)	60 °C
Luminous Flux	800 lm		
Colour designation	Cool Daylight	Controls and Dimming	
Correlated Colour Temperature	6500 K	Dimmable	No
Luminous efficacy (rated) (nom.)	88.00 lm/W		
Colour consistency	<6	Mechanical and Housing	
Colour rendering index (CRI)	83	Bulb material	Glass
LLMF at end of nominal lifetime (nom.)	70 %	Product length	600 mm
Operating and Electrical			
Line Frequency	20000-80000 Hz		


CorePro LEDtube InstantFit HF

Approval and Application	
Energy-saving product	Yes
Approval marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy consumption kWh/1,000 hours	12 kWh
Product Data	
Order product name	CorePro LEDtube HF 600mm 9W865 T8 G
Full product name	CorePro LEDtube HF 600mm 9W865 T8 G

Dimensional drawing




Photometric data



Light Distribution Diagram - CorePro LEDtube HF 600mm 9W865 T8 G

Full EOC	871869665219000
Order code	65219000
Material no. (12 NC)	929001249602
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696652190
Numerator – packs per outer box	10
EAN/UPC - Case	8718696652206


Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 600mm 9W865 T8 G	27.9 mm	28 mm	589.8 mm	595.7 mm	604 mm



General uniform lighting - CorePro LEDtube HF 600mm 9W865 T8 G

CorePro LEDtube InstantFit HF

Photometric data



Spectral Power Distribution Colour - CorePro LEDtube HF 600mm 9W865

T8 G

