



Classic LEDspotMV

CLA LEDspotMV D 5.5-50W GU10 830 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Product data


General Information		Input Frequency	
Cap-Base	GU10 [GU10]	Power Consumption	5.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	30 mA
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.70
Light Technical		Voltage (Nom)	220-240 V
Color Code	830 [CCT of 3000K]	Temperature	
Beam Angle (Nom)	36 degree(s)	T-Case Maximum (Nom)	80 °C
Luminous Flux	365 lm	Controls and Dimming	
Luminous Intensity (Nom)	680 cd	Dimmable	Yes
Color Designation	White (WH)	Mechanical and Housing	
Correlated Color Temperature (Nom)	3000 K	Bulb Shape	PAR16 [PAR 2 inch/50mm]
Luminous Efficacy (rated) (Nom)	66 lm/W	Approval and Application	
Color Consistency	<6	Energy Saving Product	Yes
Color rendering index (CRI)	80	Suitable For Accent Lighting	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	6 kWh
Luminous Flux in 90° Cone (Rated)	365 lm		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic LEDspotMV

Product Data	
Order product name	CLA LEDspotMV D 5.5-50W GU10 830 36D
Full product name	CLA LEDspotMV D 5.5-50W GU10 830 36D
Full product code	871869658169800
Order code	929001254102
Material Nr. (12NC)	929001254102


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696581698
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696581704

Dimensional drawing




Product	D	C
CLA LEDspotMV D 5.5-50W GU10 830 36D	50 mm	53 mm


Photometric data



Light Distribution Diagram - CLA LEDspotMV D 5.5-50W GU10 830 36D



General uniform lighting - CLA LEDspotMV D 5.5-50W GU10 830 36D



Spectral Power Distribution Colour - CLA LEDspotMV D 5.5-50W GU10 830 36D

Classic LEDspotMV

