

Classic filament LEDbulbs

LED A60 3-60W E27 CL ND 865

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	600 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	200.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	3 W
Lamp Current (Nom)	28 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]


Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	3 kWh

Classic filament LEDbulbs

Product Data	
Order product name	LED A60 3-60W E27 CL ND 865
Full product name	LED A60 3-60W E27 CL ND 865
Full product code	871869665895600
Order code	65895600
Material Nr. (12NC)	929001262902


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696658956
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696658963

Dimensional drawing




Product	D	C
LED A60 3-60W E27 CL ND 865	60 mm	104 mm

Photometric data



Spectral Power Distribution Colour - LED A60 3-60W E27 CL ND 865

General uniform lighting - LED A60 3-60W E27 CL ND 865



Light Distribution Diagram - LED A60 3-60W E27 CL ND 865

Classic filament LEDbulbs

