

# Classic filament LEDbulbs

## CLA LEDBulb DT 4.5-40W A60 E27 CL

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Colour Code	822-827 [tunable warm white]
Luminous Flux	470 lm
Colour designation	Warm White (WW)
Luminous efficacy (rated) (nom.)	94.00 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4.5 W

Lamp current (nom.)	24 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (nom.)	220-240 V

Temperature	
T-Case maximum (nom.)	60 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	A60 [A 60 mm]


Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	No

Classic filament LEDbulbs

Energy consumption kWh/1,000 hours	5 kWh
Product Data	
Order product name	CLA LEDBulb DT 4.5-40W A60 E27 CL
Full product name	CLA LEDBulb DT 4.5-40W A60 E27 CL
Full EOC	871869665676100
Order code	65676100



Material no. (12 NC)	929001268302
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696656761
Numerator – packs per outer box	10
EAN/UPC - Case	8718696656778

Dimensional drawing




Product	D	C
CLA LEDBulb DT 4.5-40W A60 E27 CL	60 mm	110 mm

Photometric data



General uniform lighting - CLA LEDBulb DT 4.5-40W A60 E27 CL

Light Distribution Diagram - CLA LEDBulb DT 4.5-40W A60 E27 CL



Spectral Power Distribution Colour - CLA LEDBulb DT 4.5-40W A60 E27 CL

## Classic filament LEDbulbs

