

LED InstantFit Lamps

26T8/96-6500 IF FA8 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Warnings and Safety

- Philips LED T8 InstantFit lamps will only operate properly on compatible instant-start ballasts. Please refer to the Philips LED T8 InstantFit Installation Guide, which can be obtained through your local Philips Sales Representative, or visit www.philips.com/tled

Product data

General Information	
Cap-Base	FA8 [FA8]
Nominal lifetime	36,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	3,200 lm
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50000-64000 Hz
Input Frequency	50000-64000 Hz
Power Consumption	26 W
Lamp Current (Max)	210 mA
Lamp Current (Min)	160 mA

Warm-up time to 60% light	0.5 s
Voltage (Nom)	280-340 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product Length	2,400 mm

Approval and Application	
Energy Saving Product	Yes
Approval Marks	UL certificate

Product Data	
Order product name	26T8/96-6500 IF FA8 10/1
Full product name	26T8/96-6500 IF FA8 10/1
Order code	929001273612
Material Nr. (12NC)	929001273612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677466169
Numerator - Packs per outer box	10


LED InstantFit Lamps

EAN/UPC - Case	50046677466164
----------------	----------------

Dimensional drawing

Product	D	A1	A2	A3
26T8/96-6500 IF FA8 10/1	27.9 mm	2,369.8 mm	2,375.8 mm	2,387.6 mm

Photometric data



General uniform lighting - 26T8/96-6500 IF FA8 10/1

General uniform lighting - 26T8/96-6500 IF FA8 10/1

