



Essential LEDspot MR16

LED MR16 4.5-50W 36D 865 100-240V 3BC/6

Essential LEDspots MR16 are compatible with most existing fixtures with a GU5.3 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots MR16 deliver significant energy savings and minimize initial investment.

Product data

General Information	
Cap-Base	GU5.3 [GU5.3]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	400 lm
Luminous Intensity (Nom)	750 cd
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	88.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	4.5 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.4
Voltage (Nom)	100-240 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]

Approval and Application	
Suitable For Accent Lighting	Yes


Product Data	
Order product name	LED MR16 4.5-50W 36D 865 100-240V 3BC/6

Essential LEDspot MR16

Full product name	LED MR16 4.5-50W 36D 865 100-240V 3BC/6
Full product code	871869678676500
Order code	929001274891
Material Nr. (12NC)	929001274891
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718696786765
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696786772

Dimensional drawing




Product	D	C
LED MR16 4.5-50W 36D 865 100-240V 3BC/6	51 mm	49 mm

Photometric data



Spectral Power Distribution Colour - LED MR16 4.5-50W 36D 865 100-240V 3BC/6




General uniform lighting - LED MR16 4.5-50W 36D 865 100-240V 3BC/6


Light Distribution Diagram - LED MR16 4.5-50W 36D 865 100-240V 3BC/6

Essential LEDspot MR16

Lifetime



Life Expectancy Diagram - LED MR16 4.5-50W 36D 865 100-240V 3BC/6



Lumen Maintenance Diagram - LED MR16 4.5-50W 36D 865 100-240V 3BC/6

