



LED PAR30 S/L

12PAR30L/AMB/F40/827/DIM ULW

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	850 lm
Luminous Intensity (Nom)	1,500 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	70.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	12 W
Lamp Current (Nom)	110 mA

Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	85 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and Application	
Suitable For Accent Lighting	Yes
Product Data	
Order product name	12PAR30L/AMB/F40/827/DIM ULW
Full product name	12PAR30L/AMB/F40/827/DIM ULW
Order code	929001294404
Material Nr. (12NC)	929001294404
Numerator - Quantity Per Pack	1

LED PAR30 S/L



EAN/UPC - Product/Case	046677467845
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677467840

Dimensional drawing




Product	D	C
12PAR30L/AMB/F40/827/DIM ULW	95 mm	115 mm

Photometric data



Spectral Power Distribution Colour - 12PAR30L/AMB/F40/827/DIM ULW

General uniform lighting - 12PAR30L/AMB/F40/827/DIM ULW



Light Distribution Diagram - 12PAR30L/AMB/F40/827/DIM ULW

LED PAR30 S/L

