



T8

9T8 LED/36-3000 IF 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.


Product data

General Information		Warm Up Time to 60% Light (Nom)		0.1 s
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Factor (Nom)		0.9
EU RoHS compliant	Yes	Voltage (Nom)		120-277, 347 V
Nominal Lifetime (Nom)	50000 h	Temperature		
Switching Cycle	50000X	T-Ambient (Max)		45 °C
Light Technical		T-Ambient (Min)		-20 °C
Color Code	830 [CCT of 3000K]	T-Storage (Max)		65 °C
Luminous Flux (Nom)	1100 lm	T-Storage (Min)		-40 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)		50 °C
Color Consistency	<6	Controls and Dimming		
Color Rendering Index (Nom)	82	Dimmable		No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing		
Operating and Electrical		Product Length		900 mm
Input Frequency	20000-120000 Hz	Approval and Application		
Power (Rated) (Nom)	9 W	Energy Efficiency Label (EEL)		Not applicable
Lamp Current (Max)	180 mA	Energy Saving Product		Yes
Lamp Current (Min)	60 mA			
Starting Time (Nom)	0.5 s			

Approval Marks	UL certificate RoHS compliance
Product Data	
Order product name	9T8 LED/36-3000 IF 10/1
EAN/UPC - Product	046677472313
Order code	469320

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001311304
Net Weight (Piece)	0.170 kg


Dimensional drawing




TLED 3ft 900mm 10.5-25W 1100lm 3000K ND

Product	D1	D2	A1	A2	A3
9T8 LED/36-3000 IF 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm


Photometric data



LEDtube 900mm 9W G13 830 1100lm




LEDtube 600mm 7W G13




STD 600 mm 10 W /830 T8 I

T8

Lifetime



LEDtube 600mm 7W G13



LEDtube 600mm 7W G13

