



T8

13T8 LED/24-3000 IF-6U 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.


Product data

General Information		Warm Up Time to 60% Light (Nom)	
Base	G13 [Medium Bi-Pin Fluorescent]	Power Factor (Nom)	0.9
EU RoHS compliant	Yes	Voltage (Nom)	120-277, 347 V
Nominal Lifetime (Nom)	50000 h	Temperature	
Switching Cycle	50000X	T-Ambient (Max)	45 °C
Light Technical		T-Ambient (Min)	-20 °C
Color Code	830 [CCT of 3000K]	T-Storage (Max)	65 °C
Initial lumen (Nom)	2000 lm	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	50 °C
Color Consistency	<6	Controls and Dimming	
Color Rendering Index (Nom)	82	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Mechanical and Housing	
Operating and Electrical		Product Length	600 mm
Input Frequency	20000-120000 Hz	Approval and Application	
Power (Rated) (Nom)	13 W	Energy Saving Product	Yes
Lamp Current (Max)	165 mA		
Lamp Current (Min)	55 mA		
Starting Time (Nom)	0.5 s		

Approbation Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List -	
Product Data	
Order product name	13T8 LED/24-3000 IF-6U 10/1
EAN/UPC - Product	046677472351

Order code	469379
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001311804
Net Weight (Piece)	0.270 kg
Model Number	9290013118


Dimensional drawing




TLED U bent 13-32W 2000lm 3000K ND

Product	D1	D2	B	A1	D
13T8 LED/24-3000 IF-6U 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm


Photometric data



LEDtube 500mm 13W G13 830 2000lm




LEDtube 600mm 13W G13




LEDtube 500mm 13W G13 830 2000lm

Lifetime



LEDtube 600mm 7W G13



LEDtube 600mm 7W G13

