



MASTER LEDspot PAR



MAS LEDspot CLA ND 9-60W 827 PAR38 25D

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	25,000
Lighting Technology	LED
Flux measurement reference	Narrow Cone
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	750 lm
Luminous Intensity (Nom)	1,800 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	88.89 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	750 lm
Operating and Electrical	
Line Frequency	50 Hz


Input Frequency	50 Hz
Power Consumption	9 W
Lamp Current (Nom)	44 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
Approval and Application	
Energy Efficiency Class	F
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	9 kWh
EPREL Registration Number	465201

MASTER LEDspot PAR

EyeComfort	Yes
Product Data	
Order product name	MAS LEDspot CLA ND 9-60W 827 PAR38 25D
Full product name	MAS LEDspot CLA ND 9-60W 827 PAR38 25D
Full product code	871869671456000
Order code	929001322702

Material Nr. (12NC)	929001322702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696714560
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696714577

Dimensional drawing




Product	D	C
MAS LEDspot CLA ND 9-60W 827 PAR38 25D	122 mm	134 mm

Photometric data

Spectral Power Distribution Colour - MAS LEDspot CLA ND 9-60W 827 PAR38 25D

Light Distribution Diagram - MAS LEDspot CLA ND 9-60W 827 PAR38 25D



OSRAM PHOTOMETRIC LTD. PHOTOMETRIC DATA Page 1/1

Accent Lighting Spots - MAS LEDspot CLA ND 9-60W 827 PAR38 25D

MASTER LEDspot PAR

Lifetime



Life Expectancy Diagram - MAS LEDspot CLA ND 9-60W 827 PAR38 25D

Lumen Maintenance Diagram - MAS LEDspot CLA ND 9-60W 827 PAR38 25D

