



Classic filament LEDbulbs

CLA LEDBulb D 8-60W A60 B22 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Power Consumption	
Cap-Base	B22 [B22]	8 W	
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	
Switching Cycle	20,000	52 mA	
Lighting Technology	LED	Wattage Equivalent	
EU RoHS compliant	Yes	60 W	
Light Technical		Starting Time (Nom)	
Color Code	827 [CCT of 2700K]	0.5 s	
Luminous Flux	806 lm	Warm-up time to 60% light	
Color Designation	Warm White (WW)	0.5 s	
Correlated Color Temperature (Nom)	2700 K	Power Factor (Fraction)	
Luminous Efficacy (rated) (Nom)	100.00 lm/W	0.7	
Color Consistency	<6	Voltage (Nom)	
Color rendering index (CRI)	80	220-240 V	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Temperature	
Operating and Electrical		T-Case Maximum (Nom)	
Line Frequency	50 to 60 Hz	55 °C	
Input Frequency	50 to 60 Hz	Controls and Dimming	
		Dimmable	
		Yes	
		Mechanical and Housing	
		Bulb Finish	
		Clear	
		Bulb Shape	
		A60 [A 60mm]	

Classic filament LEDbulbs

Approval and Application	
Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	CLA LEDBulb D 8-60W A60 B22 827 CL
Full product name	CLA LEDBulb D 8-60W A60 B22 827 CL
Full product code	871869670946700
Order code	929001331302


Material Nr. (12NC)	929001331302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696709467
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696709474

Dimensional drawing




Product	D	C
CLA LEDBulb D 8-60W A60 B22 827 CL	60 mm	102 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb D 8-60W A60 B22 827 CL




General uniform lighting - CLA LEDBulb D 8-60W A60 B22 827 CL




Light Distribution Diagram - CLA LEDBulb D 8-60W A60 B22 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb D 8-60W A60 B22 827 CL



Lumen Maintenance Diagram - CLA LEDBulb D 8-60W A60 B22 827 CL

