



Classic filament LED candles and lustres

Classic LEDLuster D 5-40W P45 B22 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.


Product data

General Information		Power Consumption	
Cap base	B22 [B22]	Lamp current (nom.)	38 mA
Nominal lifetime	15,000 h	Wattage equivalent	40 W
Switching Cycle	20,000	Starting time (nom.)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.7
Light Technical		Voltage (nom.)	220-240 V
Colour Code	827 [CCT of 2700K]	Temperature	
Luminous Flux	470 lm	T-Case maximum (nom.)	60 °C
Colour designation	Warm White (WW)	Controls and Dimming	
Correlated Colour Temperature	2700 K	Dimmable	Yes
Luminous efficacy (rated) (nom.)	94.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (CRI)	80	Bulb shape	P45 [P 45 mm]
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input frequency	50 to 60 Hz		


Classic filament LED candles and lustres

Approval and Application	
Energy consumption kWh/1,000 hours	5 kWh
Product Data	
Order product name	CLA LEDLuster D 5-40W P45 B22 827 CL
Full product name	Classic LEDLuster D 5-40W P45 B22 827 CL
Full EOC	871869670994800
Order code	70994800

Dimensional drawing




Photometric data




Spectral Power Distribution Colour - CLA LEDLuster D 5-40W P45 B22 827 CL

Material no. (12 NC)	929001332702
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696709948
Numerator – packs per outer box	10
EAN/UPC - Case	8718696709955

Product	D	C
CLA LEDLuster D 5-40W P45 B22 827 CL	45 mm	78 mm




General uniform lighting - CLA LEDLuster D 5-40W P45 B22 827 CL




Light Distribution Diagram - CLA LEDLuster D 5-40W P45 B22 827 CL

Classic filament LED candles and lustres

Lifetime



Life Expectancy Diagram - CLA LEDLuster D 5-40W P45 B22 827 CL



Lumen Maintenance Diagram - CLA LEDLuster D 5-40W P45 B22 827 CL

