

# Classic filament LEDbulbs

## CLA LEDBulb DT 8-60W ST64 B22 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.


### Product data

|                                       |                              |                                 |           |
|---------------------------------------|------------------------------|---------------------------------|-----------|
| <b>General Information</b>            |                              | <b>Temperature</b>              |           |
| Cap-Base                              | B22 [B22]                    | Lamp Current (Nom)              | 41 mA     |
| Nominal lifetime                      | 15,000 hour(s)               | Wattage Equivalent              | 60 W      |
| Switching Cycle                       | 20,000                       | Starting Time (Nom)             | 0.5 s     |
| Lighting Technology                   | LED                          | Warm-up time to 60% light       | 0.5 s     |
| EU RoHS compliant                     | Yes                          | Power Factor (Fraction)         | 0.7       |
| <b>Light Technical</b>                |                              | Voltage (Nom)                   | 220-240 V |
| Color Code                            | 822-827 [tunable warm white] | <b>Controls and Dimming</b>     |           |
| Luminous Flux                         | 806 lm                       | Dimmable                        | Yes       |
| Color Designation                     | Warm White (WW)              | <b>Mechanical and Housing</b>   |           |
| Luminous Efficacy (rated) (Nom)       | 100.75 lm/W                  | Bulb Finish                     | Clear     |
| Color Consistency                     | <6                           | Bulb Shape                      | ST64      |
| Color rendering index (CRI)           | 80                           | <b>Approval and Application</b> |           |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %                         | Energy Consumption kWh/1000 h   | 8 kWh     |
| <b>Operating and Electrical</b>       |                              |                                 |           |
| Line Frequency                        | 50 to 60 Hz                  |                                 |           |
| Input Frequency                       | 50 to 60 Hz                  |                                 |           |
| Power Consumption                     | 8 W                          |                                 |           |

Classic filament LEDbulbs

| Product Data        |                                  |
|---------------------|----------------------------------|
| Order product name  | CLA LEDBulb DT 8-60W ST64 B22 CL |
| Full product name   | CLA LEDBulb DT 8-60W ST64 B22 CL |
| Full product code   | 871869670978800                  |
| Order code          | 929001334102                     |
| Material Nr. (12NC) | 929001334102                     |


Dimensional drawing




|                                 |               |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8718696709788 |
| Numerator - Packs per outer box | 10            |
| EAN/UPC - Case                  | 8718696709795 |

| Product                          | D     | C      |
|----------------------------------|-------|--------|
| CLA LEDBulb DT 8-60W ST64 B22 CL | 64 mm | 138 mm |


Photometric data



Spectral Power Distribution Colour - CLA LEDBulb DT 8-60W ST64 B22 CL




General uniform lighting - CLA LEDBulb DT 8-60W ST64 B22 CL




Light Distribution Diagram - CLA LEDBulb DT 8-60W ST64 B22 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb DT 8-60W ST64 B22 CL



Lumen Maintenance Diagram - CLA LEDBulb DT 8-60W ST64 B22 CL

