



MASTER LEDspot ExpertColor LV

MAS LED MR16 ExpertColor 7.2-50W 927 60D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Product data


General Information		LLMF At End Of Nominal Lifetime (Nom) 70 %	
Cap-Base	GU5.3 [GU5.3]		
Nominal lifetime	40,000 hour(s)		
Switching Cycle	50,000		
Lighting Technology	LED		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Color Code	927	Line Frequency	- Hz
Beam Angle (Nom)	60 degree(s)	Input Frequency	- Hz
Luminous Flux	450 lm	Power Consumption	7.2 W
Luminous Intensity (Nom)	410 cd	Lamp Current (Nom)	800 mA
Color Designation	Warm White (WW)	Wattage Equivalent	50 W
Correlated Color Temperature (Nom)	2700 K	Starting Time (Nom)	0.5 s
Luminous Efficacy (rated) (Nom)	62.50 lm/W	Warm-up time to 60% light	1 s
Color Consistency	<3	Power Factor (Fraction)	0.7
Color rendering index (CRI)	97	Voltage (Nom)	12 V
		Temperature	
		T-Case Maximum (Nom)	92 °C

MASTER LEDspot ExpertColor LV

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	MAS LED MR16 ExpertColor 7.2-50W 927 60D


Full product name	MAS LED MR16 ExpertColor 7.2-50W 927 60D
Full product code	871869671950300
Order code	929001341408
Material Nr. (12NC)	929001341408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696719503
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696719510

Dimensional drawing




Product	D	C
MAS LED MR16 ExpertColor 7.2-50W 927 60D	50.5 mm	46 mm

Photometric data




Spectral Power Distribution Colour - MAS LED MR16 ExpertColor 7.2-50W 927 60D



Accent Lighting Spots - MAS LED MR16 ExpertColor 7.2-50W 927 60D


MASTER LEDspot ExpertColor LV

Photometric data




Light Distribution Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 60D

Lifetime



Life Expectancy Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 60D



Lumen Maintenance Diagram - MAS LED MR16 ExpertColor 7.2-50W 927 60D

