



# MASTER LEDspot ExpertColor LV

## MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 60D

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customised spectrum, high CRI and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV lamps.

### Product data

General Information	
Cap base	GU5.3 [ GU5.3]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	40000 h
Switching cycle	50,000X
Technical type	6.5-35W
Light Technical	
Colour code	930 [ CCT of 3,000 K]
Beam Angle (Nom)	60 °
Luminous flux (nom.)	440 lm
Luminous intensity (nom.)	440 cd
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	67.69 lm/W
Colour consistency	<3


Color rendering index (nom.)	97
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	440 lm
Operating and Electrical	
Input frequency	- Hz
Power (Rated) (Nom)	6.5 W
Lamp current (nom.)	800 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	ac electronic 12 V

# MASTER LEDspot ExpertColor LV

<b>Temperature</b>	
T-Case maximum (nom.)	90 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	8 kWh
<b>Product Data</b>	
Full product code	871869675753600

Order product name	MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 60D
EAN/UPC – product	8718696757536
Order code	75753600
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001341502
Net weight (piece)	0.034 kg


## Dimensional drawing




MAS LED MR16 ExpertColor 7.2-50W 930 60D

Product	D	C
MASTER LED ExpertColor LED ExpertColor 6.5-35W MR16 930 60D	50.5 mm	46 mm

## Photometric data



Master LEDspot ExpertColor LV 50W EZ10 930 10D





Master LEDspot ExpertColor LV 50W GU5.3 930 60D

# MASTER LEDspot ExpertColor LV

## Photometric data

Master LEDspot ExpertColor LV 50W GU5.3 930 60D

### Lifetime



Master LEDspot ExpertColor LV 50W EZ10 927 10D

Master LEDspot ExpertColor LV 50W EZ10 927 10D

