



Classic frosted LED candles and lusters

CLA LEDLuster ND 2.2-25W P45 E27 FR

Featuring a classic heritage design, Classic forsted LED candles and lusters deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of Classic forsted LED candles and lusters are a perfect fit for your existing fixtures.

Product data


General Information		Input Frequency	
Cap-Base	E27 [E27]	Power Consumption	2.2 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	21 mA
Switching Cycle	20,000	Wattage Equivalent	25 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
Flux measurement reference	Sphere	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.4
Light Technical		Voltage (Nom)	220-240 V
Color Code	827 [CCT of 2700K]	Temperature	
Luminous Flux	250 lm	T-Case Maximum (Nom)	36 °C
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	113.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color rendering index (CRI)	80	Bulb Shape	P45 [P 45mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic frosted LED candles and lusters

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	3 kWh
EPREL Registration Number	387385
EyeComfort	Yes
Product Data	
Order product name	CLA LEDLuster ND 2.2-25W P45 E27 FR
Full product name	CLA LEDLuster ND 2.2-25W P45 E27 FR


Full product code	871869670645900
Order code	929001345602
Material Nr. (12NC)	929001345602
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696706459
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696706466

Dimensional drawing




Product	D	C
CLA LEDLuster ND 2.2-25W P45 E27 FR	45 mm	78 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDLuster ND 2.2-25W P45 E27 FR




General uniform lighting - CLA LEDLuster ND 2.2-25W P45 E27 FR



Light Distribution Diagram - CLA LEDLuster ND 2.2-25W P45 E27 FR

Classic frosted LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDLuster ND 2.2-25W P45 E27 FR

Lumen Maintenance Diagram - CLA LEDLuster ND 2.2-25W P45 E27 FR

